







Number of contacts

# 12+

16 A 830 V 8 kV 3  
+ 4 additional relay contacts

Han  
Hv E

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han Hv E®, Crimp termination</p>  <p>Please order crimp contacts separately. You need two inserts for a complete assembly!</p>	0.5 ... 4	09 34 006 2602	09 34 006 2702	
<p>Han Hv E®, Screw termination, With wire protection, Contact surface: Silver plated</p>  <p>You need two inserts for a complete assembly!</p>	0.75 ... 2.5	09 34 006 2601	09 34 006 2701	  <p><b>M</b>                      <b>F</b> Contact arrangement (view from termination side) Han® 12 Hv E ◆ Power contacts ● Relay contact ○ Without contact</p>  <p>Panel cut out for use without Hoods/Housings</p>