









Number of contacts

20+

16 A 830 V 8 kV 3
+ 4 additional relay contacts

Han
Hv E

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han Hv E®, Crimp termination</p>  <p>Please order crimp contacts separately. You need two inserts for a complete assembly!</p>	0.5 ... 4	09 34 010 2602	09 34 010 2702	
<p>Han Hv E®, Screw termination, With wire protection, Contact surface: Silver plated</p>  <p>You need two inserts for a complete assembly!</p>	0.75 ... 2.5	09 34 010 2601	09 34 010 2701	  <p>M F Contact arrangement (view from termination side) Han® 20 Hv E</p> <ul style="list-style-type: none"> ● Power contacts ● Relay contact ○ Without contact  <p>Panel cut out for use without Hoods/Housings</p>