






Number of contacts

27

2 A 16 V 0.8 kV 3
+ shielding

Modular

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
Han-Modular®, Adapter module, Han® Gigabit module, Han® Shielded module, Han® Megabit module 		09 14 001 3011	09 14 001 3111	
Han-Modular®, Han® High density shielded module, Crimp termination  <p>Please order crimp contacts separately.</p>	0.13 ... 0.33	09 14 027 3013	09 14 027 3113	
Circular connectors M12, Crimp contact, Contact surface: Gold plated 	0.13 ... 0.33	21 01 100 9020	21 01 100 9025	