









Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)															
		Male	Female																
Han-Modular®, Han-Quintax® module, Crimp termination 		09 14 002 3004	09 14 002 3104																
Han-Quintax® High Density, for Han® D-Sub crimp contacts  <p>Please order crimp contacts separately.</p>	0.09 ... 0.52	09 15 008 3013	09 15 008 3113	 <p>Cable diameter 3 ... 9.5 mm</p>															
Han-Quintax®, Adapter, Metal 		09 14 000 9915	09 14 000 9915																
Optional D-Sub, Standard, Crimp contact 	0.09 ... 0.25 0.13 ... 0.33 0.25 ... 0.52	09 67 000 7576 09 67 000 5576 09 67 000 8576	09 67 000 7476 09 67 000 5476 09 67 000 8476	 <table border="1" data-bbox="997 1758 1452 1904"> <thead> <tr> <th>Conductor cross-section</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.09-0.25 mm<sup>2</sup></td> <td>0.64 mm</td> <td>4 mm</td> </tr> <tr> <td>0.13-0.33 mm<sup>2</sup></td> <td>0.88 mm</td> <td>4 mm</td> </tr> <tr> <td>0.25-0.52 mm<sup>2</sup></td> <td>1.13 mm</td> <td>4 mm</td> </tr> <tr> <td>0.33-0.82 mm<sup>2</sup></td> <td>1.34 mm</td> <td>4 mm</td> </tr> </tbody> </table> <p>for stranded wire according IEC 60228 Class 5</p>	Conductor cross-section	Ø	Stripping length	0.09-0.25 mm <sup>2</sup>	0.64 mm	4 mm	0.13-0.33 mm <sup>2</sup>	0.88 mm	4 mm	0.25-0.52 mm <sup>2</sup>	1.13 mm	4 mm	0.33-0.82 mm <sup>2</sup>	1.34 mm	4 mm
Conductor cross-section	Ø	Stripping length																	
0.09-0.25 mm <sup>2</sup>	0.64 mm	4 mm																	
0.13-0.33 mm <sup>2</sup>	0.88 mm	4 mm																	
0.25-0.52 mm <sup>2</sup>	1.13 mm	4 mm																	
0.33-0.82 mm <sup>2</sup>	1.34 mm	4 mm																	