

Number of contacts

# 3



Modular

## Features





- for the transmission of clean and dry compressed air
- Female contacts with / without shut-off
- The Han® Pneumatic contacts without shut-off are suitable for the use inside a vacuum. (Limit: 100 mbar = 100 hPa ≈ approx 90% vacuum)

## Technical characteristics

Number of contacts	3
Limiting temperature	-40 ... +85 °C, -20 ... +85 °C
Operating pressure	≤10 bar
Mating cycles	≥10000
Tube inner diameter	3 mm, 4 mm, 6 mm
Tube outer diameter	3 mm, 4 mm, 6 mm
Material (insert)	Polycarbonate (PC)
Colour (insert)	Blue
Material (seal)	NBR
Colour (seal)	Black
Material (contacts)	Brass
Material flammability class acc. to UL 94	V-0
RoHS	compliant, compliant with exemption

## Specifications and approvals

IEC 61984  
 EN 60664-1  
 UL 1977 ECBT2.E235076  
 CSA-C22.2 No. 182.3 ECBT8.E235076

Identification	Part number		Drawing (dimensions in mm)
	Male	Female	
Han-Modular®, Han® Pneumatic module  <p>Please order contacts separately.</p> <p>Pneumatic contact,                      Without shut-off,                      Straight,                      Tube outer diameter</p> 			 <p>Contact arrangement (view from mating side)</p> 
	09 14 003 3501	09 14 003 3501	
	09 14 000 6353 09 14 000 6354 09 14 000 6356	09 14 000 6453 09 14 000 6454 09 14 000 6456	