

Number of contacts

# 6

Modular

## Features

- Suitable for HARTING LC contacts
- for GI-Fibre 50 - 62.5 / 125 µm and for singlemode fibre



## Technical characteristics

Number of contacts	6
Limiting temperature	-40 ... +85 °C
Mating cycles	≥500
Material (insert)	Polycarbonate (PC)
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant

## Details

The male and female modules each use the same contacts.

ATTENTION! Guide pins and bushes are prescribed (see chapter Han 80).

Identification	Part number		Drawing (dimensions in mm)
	Male	Female	
Han-Modular®, Han® LC module  <p>Please order contacts separately.</p>	09 14 006 4701	09 14 006 4711	 <p>Contact arrangement (view from termination side)</p>