





Number of contacts

40+

10 A 250 V 4 kV 3

Han AV

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)	
		Male	Female		
<p>Han D® AV, Terminal block connector, Left hand version, Multi contour (MK), Screw termination, Contact surface: Silver plated</p> 	0.2 ... 2.5	09 21 040 4601	09 21 040 4701		
<p>Han D® AV, Terminal block connector, Left hand version, Single contour (SK), Screw termination, Contact surface: Silver plated</p> 	0.2 ... 2.5	09 21 040 4602	09 21 040 4702	