






Number of contacts

**4+**

10 A 230/400 V 4 kV 3  
10 A 250 V 4 kV 3

Han A

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han A<sup>®</sup>, Han-Quick Lock<sup>®</sup> termination, Contact surface: Silver plated</p>  <p>Blue slide</p>	0.5 ... 2.5	09 20 004 2633	09 20 004 2733	 <p>Contact arrangement (view from termination side)</p>
<p>Han A<sup>®</sup>, Han-Quick Lock<sup>®</sup> termination, Contact surface: Silver plated</p>  <p>Black slide</p>	0.25 ... 1.5	09 20 004 2634	09 20 004 2734	
<p>Han A<sup>®</sup>, Screw termination, Contact surface: Silver plated</p> 	0.75 ... 1.5	09 20 004 2611	09 20 004 2711	 <p>Contact arrangement (view from termination side) Stripping length 4.5 mm Tightening torque 0.25 Nm</p>