








Number of contacts

10+

16 A 500 V 6 kV 3

Han
AV

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)	
		Male	Female		
<p>Han® ES AV, Terminal block connector, Left hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated</p> 	0.14 ... 2.5	09 33 010 4629	09 33 010 4729		
<p>Han® ES AV, Terminal block connector, Right hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated</p> 	0.14 ... 2.5	09 33 010 4639	09 33 010 4739		
<p>Han® ES AV, Terminal block connector, Right hand version, Single contour (SK), Cage-clamp termination, Contact surface: Silver plated</p> 	0.14 ... 2.5	09 33 010 4639	09 33 010 4739	