

Number of contacts

# 2+

40 A 830 V 6 kV 3

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)																		
		Male	Female																			
<p>Han® Q, 2/0 High Voltage, Crimp termination, Pack contents: With heat shrink tube</p> <p>Please order crimp contacts separately.</p>	1.5 ... 10	09 12 002 3052	09 12 002 3152	<p>Contact arrangement (view from termination side)</p>																		
<p>Han® C, Crimp contact, Contact surface: Silver plated</p>	1.5 2.5 4 6 10	09 32 000 6104 09 32 000 6105 09 32 000 6107 09 32 000 6108 09 32 000 6109	09 32 000 6204 09 32 000 6205 09 32 000 6207 09 32 000 6208 09 32 000 6209	<table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>1.5 mm<sup>2</sup> AWG 16</td> <td>1.75 mm</td> <td>9.5 mm</td> </tr> <tr> <td>2.5 mm<sup>2</sup> AWG 14</td> <td>2.25 mm</td> <td>9.5 mm</td> </tr> <tr> <td>4 mm<sup>2</sup> AWG 12</td> <td>2.85 mm</td> <td>9.5 mm</td> </tr> <tr> <td>6 mm<sup>2</sup> AWG 10</td> <td>3.5 mm</td> <td>9.5 mm</td> </tr> <tr> <td>10 mm<sup>2</sup> AWG 8</td> <td>4.3 mm</td> <td>12 mm</td> </tr> </tbody> </table>	Conductor cross-section	Ø	Stripping length	1.5 mm <sup>2</sup> AWG 16	1.75 mm	9.5 mm	2.5 mm <sup>2</sup> AWG 14	2.25 mm	9.5 mm	4 mm <sup>2</sup> AWG 12	2.85 mm	9.5 mm	6 mm <sup>2</sup> AWG 10	3.5 mm	9.5 mm	10 mm <sup>2</sup> AWG 8	4.3 mm	12 mm
Conductor cross-section	Ø	Stripping length																				
1.5 mm <sup>2</sup> AWG 16	1.75 mm	9.5 mm																				
2.5 mm <sup>2</sup> AWG 14	2.25 mm	9.5 mm																				
4 mm <sup>2</sup> AWG 12	2.85 mm	9.5 mm																				
6 mm <sup>2</sup> AWG 10	3.5 mm	9.5 mm																				
10 mm <sup>2</sup> AWG 8	4.3 mm	12 mm																				
<p>Coding element</p>		09 12 000 9922																				