






Han Q

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)																												
		Male	Female																													
Han D®, Crimp contact, Contact surface: Gold plated 	0.14 ... 0.37	09 15 000 6124	09 15 000 6224	 <table border="1" data-bbox="957 492 1420 672"> <thead> <tr> <th>Conductor cross-section</th> <th>AWG</th> <th>Ø</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm²</td> <td>AWG 26-22</td> <td>0.9 mm</td> <td>8 mm</td> </tr> <tr> <td>0.5 mm²</td> <td>AWG 20</td> <td>1.1 mm</td> <td>8 mm</td> </tr> <tr> <td>0.75 mm²</td> <td>AWG 18</td> <td>1.3 mm</td> <td>8 mm</td> </tr> <tr> <td>1 mm²</td> <td>AWG 18</td> <td>1.45 mm</td> <td>8 mm</td> </tr> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75 mm</td> <td>8 mm</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25 mm</td> <td>6 mm</td> </tr> </tbody> </table>	Conductor cross-section	AWG	Ø	Stripping length	0.14-0.37 mm ²	AWG 26-22	0.9 mm	8 mm	0.5 mm ²	AWG 20	1.1 mm	8 mm	0.75 mm ²	AWG 18	1.3 mm	8 mm	1 mm ²	AWG 18	1.45 mm	8 mm	1.5 mm ²	AWG 16	1.75 mm	8 mm	2.5 mm ²	AWG 14	2.25 mm	6 mm
	Conductor cross-section	AWG	Ø		Stripping length																											
	0.14-0.37 mm ²	AWG 26-22	0.9 mm		8 mm																											
	0.5 mm ²	AWG 20	1.1 mm		8 mm																											
	0.75 mm ²	AWG 18	1.3 mm		8 mm																											
	1 mm ²	AWG 18	1.45 mm		8 mm																											
1.5 mm ²	AWG 16	1.75 mm	8 mm																													
2.5 mm ²	AWG 14	2.25 mm	6 mm																													
0.5	09 15 000 6123	09 15 000 6223																														
0.75	09 15 000 6125	09 15 000 6225																														
1	09 15 000 6122	09 15 000 6222																														
1.5	09 15 000 6121	09 15 000 6221																														
2.5	09 15 000 6126	09 15 000 6226																														
FO contact, for 1 mm plastic fibre 		20 10 001 3211	20 10 001 3221	 <p>20 10 001 3211 + 20 10 001 3221</p>																												
Coding element, Pack contents: 20 pieces per frame 		09 12 000 9924		