




Number of contacts

# 8

5 A 50 V 0.8 kV 3

Han Q

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)															
		Male	Female																
<p>Han® Q, Data RJ45, Crimp termination</p>  <p>Please order crimp contacts separately.</p>	0.13 ... 0.52	09 12 011 3001	09 12 011 3111																
<p>D-Sub, Standard, Crimp contact</p> 	0.13 ... 0.33 0.25 ... 0.52	09 67 000 5576 09 67 000 8576	09 67 000 5476 09 67 000 8476	<table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.09-0.25 mm<sup>2</sup></td> <td>0.64 mm</td> <td>4 mm</td> </tr> <tr> <td>0.13-0.33 mm<sup>2</sup></td> <td>0.88 mm</td> <td>4 mm</td> </tr> <tr> <td>0.25-0.52 mm<sup>2</sup></td> <td>1.13 mm</td> <td>4 mm</td> </tr> <tr> <td>0.33-0.82 mm<sup>2</sup></td> <td>1.34 mm</td> <td>4 mm</td> </tr> </tbody> </table> <p>for stranded wire according IEC 60228 Class 5</p>	Conductor cross-section	∅	Stripping length	0.09-0.25 mm <sup>2</sup>	0.64 mm	4 mm	0.13-0.33 mm <sup>2</sup>	0.88 mm	4 mm	0.25-0.52 mm <sup>2</sup>	1.13 mm	4 mm	0.33-0.82 mm <sup>2</sup>	1.34 mm	4 mm
Conductor cross-section	∅	Stripping length																	
0.09-0.25 mm <sup>2</sup>	0.64 mm	4 mm																	
0.13-0.33 mm <sup>2</sup>	0.88 mm	4 mm																	
0.25-0.52 mm <sup>2</sup>	1.13 mm	4 mm																	
0.33-0.82 mm <sup>2</sup>	1.34 mm	4 mm																	