








Hoods/housings for industrial applications  
Single locking lever

Han Q

| Identification  | Cable entry                    | Part number  | Drawing<br>(dimensions in mm)  |  |
|---|--------------------------------|--|--|--|
| Han-Compact®,<br>Hood,<br>for Han-Compact® half cable gland,<br>Top entry,<br>IP65<br><br>         | 1x M25<br>1x Pg 16<br>1x Pg 21 | 19 12 008 0429<br>09 12 008 0427<br>09 12 008 0429 |    |  |
| Han-Compact®,<br>Hood,<br>for flexible conduits Adaptaflex PAFS18,<br>Top entry,<br>IP65<br><br> | 1x PAFS 18                     | 09 12 008 0428                                     |  |  |
| Han-Compact®,<br>Hood,<br>for Han-Compact® half cable gland,<br>Side entry,<br>IP65<br><br>      | 1x Pg 16                       | 09 12 008 0527                                     |  |  |
| Han-Compact®,<br>Hood,<br>Top/side entry,<br>IP65<br><br>  | 2x M20                         | 19 12 008 0425                                     |  |  |