





Number of contacts

3

200 A 1.150/2.000 V 8 kV 3



Han  
HC

Identification	Conductor cross-section (mm <sup>2</sup> )	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han-Com®, Han® K 3/0, Straight, Axial screw termination, Contact surface: Silver plated</p> 	35 ... 70	09 38 005 2621	09 38 005 2721	 <p>Distance for contact max. 21 mm Stripping length 22 mm Tightening torque 8 Nm @ 35 mm<sup>2</sup>, 9 Nm @ 50 mm<sup>2</sup>, 10 Nm @ 70 mm<sup>2</sup></p>
<p>Han-Com®, Han® K 3/0, Angled, Axial screw termination, Contact surface: Silver plated</p> 	35 ... 70	09 38 005 2622	09 38 005 2722	 <p>Distance for contact max. 21 mm Stripping length 22 mm Tightening torque 8 Nm @ 35 mm<sup>2</sup>, 9 Nm @ 50 mm<sup>2</sup>, 10 Nm @ 70 mm<sup>2</sup></p>