





350 A 2.000 V 12 kV 3

Han
HC

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)
		Male	Female	
<p>Han® HC Modular, 350, Screw termination, Contact surface: Silver plated</p> 	120	09 11 001 2655	09 11 001 2755	 <p>Tightening torque 14 Nm Cable shoe ≤ 120 mm² Please ensure to hold up the contact with a wrench size 17 to apply the tightening torque</p>
<p>TC 350, PE contact, Screw termination, Contact surface: Silver plated</p> 	120	09 11 000 6158	09 11 000 6258	 <p>Tightening torque 14 Nm Cable shoe ≤ 120 mm² Please ensure to hold up the contact with a wrench size 17 to apply the tightening torque</p>