









Han
HC

Identification	Cable entry	Conductor cross-section (mm ²)	Part number	Drawing (dimensions in mm)
<p>Han® HPR EasyCon, Frame, for female inserts, 4x Han® HC Modular 350,</p> <p>Pack contents: 2x distance bolt (A/F 7), 4x M4 screw, 4x washer SK S4, 4x heat shrink tube</p> 			09 40 024 9914	 <p>Tightening torque Distance bolt 6 Nm Tightening torque Fixing screws M4: 1.5 Nm</p>
<p>Han® HPR EasyCon, Frame, for male inserts, 3x Han® HC Modular 650,</p> <p>Pack contents: 2x distance bolt (A/F 7), 2x M4 screw, 2x washer SK S4, 2x M4 countersunk screw</p> 			09 40 024 9921	 <p>Tightening torque Distance bolt 6 Nm Tightening torque Fixing screws M4: 1.5 Nm Tightening torque M4: 1.5 Nm</p>
<p>Han® HPR EasyCon, Frame, for female inserts, 3x Han® HC Modular 650,</p> <p>Pack contents: 2x distance bolt (A/F 7), 2x M4 screw, 2x washer SK S4, 2x M4 countersunk screw</p> 			09 40 024 9922	 <p>Tightening torque Distance bolt 6 Nm Tightening torque Fixing screws M4: 1.5 Nm Tightening torque M4: 1.5 Nm</p>
<p>Han® HPR EasyCon, Frame, for up to 8 single modules, A ... H,</p> <p>Pack contents: 2x M4/M5 distance bolts (A/F 7), 2x M5/M6 distance bolts (A/F 7), 4x M4 screw, 4x washer SK S4</p> 			09 40 024 9931	 <p>Tightening torque Distance bolt 6 Nm Tightening torque Fixing screws M4: 1.5 Nm Tightening torque M4: 1.5 Nm</p>