







Double locking lever

Han
Eco

| Identification | Cable entry | Clamping range (mm) | Part number | Drawing (dimensions in mm) |
|--|-------------|---------------------|----------------|---|
| Han-Eco® Modular, Hood, With integrated cable gland, Top entry, IP65  | 1x M40 | 16 ... 28 | 19 41 124 0423 |  |
| Han-Eco® Modular, Hood, With integrated cable gland, Side entry, IP65  | 1x M40 | 16 ... 28 | 19 41 124 0523 |  |
| Han-Eco® Modular, Bulkhead mounted housing, IP65  | | | 19 41 224 0301 |  <p>Panel cut out</p> |