







Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
<p>Han-Eco® B, Surface mounted housing, With integrated cable gland, Side entry, IP66</p> 	<p>1x M25 1x M32 1x M40 2x M25 2x M32 2x M40</p>	<p>9 ... 17 13 ... 21 16 ... 28 9 ... 17 13 ... 21 16 ... 28</p>	<p>19 43 116 0251 19 43 116 0252 19 43 116 0253 19 43 116 0291 19 43 116 0292 19 43 116 0293</p>	
<p>Han-Eco® B, Surface mounted housing, With thermo-plastic cover, With integrated cable gland, Side entry, IP66</p> 	<p>1x M25 1x M32 1x M40 2x M25 2x M32 2x M40</p>	<p>9 ... 17 13 ... 21 16 ... 28 9 ... 17 13 ... 21 16 ... 28</p>	<p>19 43 116 0256 19 43 116 0257 19 43 116 0258 19 43 116 0296 19 43 116 0297 19 43 116 0298</p>	
<p>Han-Eco® B, Cable to cable housing, With integrated cable gland, Top entry, IP66</p> 	<p>1x M25 1x M32 1x M40</p>	<p>9 ... 17 13 ... 21 16 ... 28</p>	<p>19 43 116 0756 19 43 116 0757 19 43 116 0758</p>	
<p>Han-Eco® B, Protection cover, for hoods, IP66</p> <p>Han-Eco® B, Protection cover, for bulkhead mounted housings, for surface mounted housings, IP66</p> <p>Han-Eco® B, Protection cover, for cable to cable housing, IP66</p>			<p>19 43 016 5442</p> <p>19 43 016 5410</p> <p>19 43 016 5446</p>	