







Double locking lever (on the hood)

Han
Eco

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
Han-Eco® B, Hood, With integrated cable gland, Top entry, IP66 	1x M40	16 ... 28	19 43 124 0438	
Han-Eco® B, Hood, With integrated cable gland, Side entry, IP66 	1x M40	16 ... 28	19 43 124 0538	
Han-Eco® B, Bulkhead mounted housing, With thermo-plastic cover, IP66 			19 43 024 0322	 <p>Panel cut out Front mounting / Rear mounting</p>