






Single locking lever

Han
Eco

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
<p>Han-Eco® B, Hood, With integrated cable gland, Top entry, IP66</p> 	<p>1x M20 1x M25 1x M32</p>	<p>6 ... 13 9 ... 17 13 ... 21</p>	<p>19 43 106 0445 19 43 106 0446 19 43 106 0447</p>	
<p>Han-Eco® B, Hood, With integrated cable gland, Side entry, IP66</p> 	<p>1x M20 1x M25 1x M32</p>	<p>6 ... 13 9 ... 17 13 ... 21</p>	<p>19 43 106 0545 19 43 106 0546 19 43 106 0547</p>	
<p>Han-Eco® B, Bulkhead mounted housing, IP66</p> 			<p>19 43 206 0340</p>	