





| Identification  | Cable entry   | Clamping range (mm)  | Part number   | Drawing (dimensions in mm)   |
|---|---|--|---|--|
| <p>Han-Eco® B,<br/>Bulkhead mounted housing,<br/>Without frame,<br/>IP66</p>  <p>Please order frame 19 43 010 0001 separately.</p> |   |  | 19 43 210 0310  |  <p>Panel cut out<br/>Front mounting / Rear mounting</p> |
| <p>Han-Eco® B,<br/>Surface mounted housing,<br/>With integrated cable gland,<br/>Side entry,<br/>IP66</p>                        | <p>1x M20<br/>1x M25<br/>1x M32<br/>1x M40<br/>2x M20<br/>2x M25<br/>2x M32</p> | <p>6 ... 13<br/>9 ... 17<br/>13 ... 21<br/>16 ... 28<br/>6 ... 13<br/>9 ... 17<br/>13 ... 21</p> | <p>19 43 310 0230<br/>19 43 310 0231<br/>19 43 310 0232<br/>19 43 310 0233<br/>19 43 310 0270<br/>19 43 310 0271<br/>19 43 310 0272</p> |   |