







Double locking lever

Han Eco

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)	
Han-Eco® B, Hood, With integrated cable gland, Top entry, IP66 	1x M25 1x M32 1x M40	9 ... 17 13 ... 21 16 ... 28	19 43 116 0426 19 43 116 0427 19 43 116 0428		
Han-Eco® B, Hood, With integrated cable gland, Side entry, IP66 	1x M25 1x M32 1x M40	9 ... 17 13 ... 21 16 ... 28	19 43 116 0526 19 43 116 0527 19 43 116 0528		
Han-Eco® B, Bulkhead mounted housing, IP66 			19 43 216 0320	 <p data-bbox="994 1877 1318 1921">Panel cut out Front mounting / Rear mounting</p>	