







Double locking lever

Han Eco

Identification	Cable entry	Clamping range (mm)	Part number	Drawing (dimensions in mm)
<p>Han-Eco® B, Hood, With integrated cable gland, Top entry, IP66</p> 	<p>1x M32 1x M40</p>	<p>13 ... 21 16 ... 28</p>	<p>19 43 124 0427 19 43 124 0428</p>	
<p>Han-Eco® B, Hood, With integrated cable gland, Side entry, IP66</p> 	<p>1x M32 1x M40</p>	<p>13 ... 21 16 ... 28</p>	<p>19 43 124 0527 19 43 124 0528</p>	
<p>Han-Eco® B, Bulkhead mounted housing, IP66</p> 			<p>19 43 224 0320</p>	 <p>Panel cut out Front mounting / Rear mounting</p>