


PROFINET Type B cable, Hybrid  
Industrial Cat. 5 Hybrid cable, 4-wire + 4x Power  
to make up Hybrid system cables



Han

## Advantages

- Robust design for industrial environment
- PROFINET-conform
- Additional power supply
- Hybrid Cat. 5 cable, 4-wire + 4x Power

## Technical characteristics

Cable construction	Star quad + 4 Power cables, double shielded
Core structure	4 x AWG 22/7 + 4 x 1.5 mm <sup>2</sup> (conductor 84 x 0.15 mm <sup>2</sup> )
Sheath material	FRNC
Cable outer diameter	9.7 mm
Transmission performance	Category 5 / Class D up to 100 MHz acc. to ISO/IEC 11801:2002, EN 50 173-1
Transmission rate	10/100 Mbit/s
Shielding	Shielding foil and shielding braid
Temperature range	-20 °C ... +70 °C
Standard lengths	10 m / 20 m / 50 m / 100 m
Colour	green

### Identification


PROFINET Type B cable, Hybrid  
Industrial Cat. 5 Hybrid cable,  
4-wire + 4x Power

10 m ring  
20 m ring  
50 m ring  
100 m ring  
500 m reel

### Part number

09 45 600 0310  
09 45 600 0330  
09 45 600 0340  
09 45 600 0300  
09 45 600 0320

### Drawing



### Dimensions in mm