













Hybrid network connector  
+ 2 electrical contacts 10 A



Identification	Part number	Drawing	Dimensions in mm
Han-Brid® RJ45 C with RJ Industrial 	<b>09 12 003 3011</b>		21, 21, 44, 26,2
Han-Brid® RJ45 C with Stewart RJ45 	<b>09 12 003 3021</b>		21, 21, 36,6, 26,2
Han-Brid® RJ45 C with HIROSE RJ45 	<b>09 12 003 3031</b>		21, 21, 37,8, 26,2
Panel feed-through straight 	<b>09 12 003 2774</b>		21, 21, 51,5, 27,3
Panel feed-through angled 	<b>09 12 003 2776</b>		21, 25,8, 21, 50,1, 27,3
Panel feed-through with 4-pole terminal block 	<b>09 12 003 2770</b>		21, 21, 42,9, 27,3