


















Identification		Part number	M	Drawing	Dimensions in mm
Hoods	Hoods side-entry 	grey 19 20 003 0620 black 19 20 003 0627	20 20		
	Hoods top-entry 	grey 19 20 003 0420 black 19 20 003 0427	20 20		
	Protection covers for hoods	09 20 003 5442 ¹⁾ 09 20 003 5441 ²⁾			
Housings	Housings bulkhead mounting 	grey 09 20 003 0320 black 09 20 003 0327 grey 09 20 003 0820 black 09 20 003 0827	- - - -	Panel cut out 22 x 22 mm 	
	Housings surface mounting 1 side-entry 	grey 19 20 003 0220 black 19 20 003 0227	20 20	Panel cut out 22 x 22 mm 	
	Hoods cable to cable 	grey 19 20 003 0720 black 19 20 003 0727	20 20		
	Protection covers for housings A 	09 20 003 5407 ¹⁾ 09 20 003 5408²⁾			
	Protection covers for housings B 	09 20 003 5445²⁾ 09 20 003 5446 ¹⁾ 09 20 003 5447 ²⁾ ³⁾			
Protection covers for hoods cable to cable C 	09 20 003 5448 ¹⁾ 09 20 003 5449 ²⁾				

Han

1) for mounted male insert
2) for mounted female or Han-Brid® insert
3) for metal housings and cable to cable hoods also

Stock items in bold type