


Number of contacts

6-64



Low-profile male header, straight press-in pins


| Identification | No. of contacts | Part number | Drawing | Dimensions in mm |
|----------------|-----------------|-------------|---------|------------------|
|----------------|-----------------|-------------|---------|------------------|

Low-profile male header with straight press-in terminations
Length: 5.5 mm


| | |
|----|-----------------|
| 6 | 09 18 506 □ 329 |
| 10 | 09 18 510 □ 329 |
| 14 | 09 18 514 □ 329 |
| 16 | 09 18 516 □ 329 |
| 20 | 09 18 520 □ 329 |
| 26 | 09 18 526 □ 329 |
| 34 | 09 18 534 □ 329 |
| 40 | 09 18 540 □ 329 |
| 50 | 09 18 550 □ 329 |
| 60 | 09 18 560 □ 329 |
| 64 | 09 18 564 □ 329 |

| No. of contacts | A | B | E |
|-----------------|------|-------|-------------------|
| 6 | 15.2 | 12.78 | 2.54 x 2 = 5.08 |
| 10 | 20.3 | 17.86 | 2.54 x 4 = 10.16 |
| 14 | 25.4 | 22.94 | 2.54 x 6 = 15.24 |
| 16 | 27.9 | 25.48 | 2.54 x 7 = 17.78 |
| 20 | 33.0 | 30.56 | 2.54 x 9 = 22.86 |
| 26 | 40.6 | 38.18 | 2.54 x 12 = 30.48 |
| 34 | 50.8 | 48.34 | 2.54 x 16 = 40.64 |
| 40 | 58.4 | 55.96 | 2.54 x 19 = 48.26 |
| 50 | 71.3 | 68.66 | 2.54 x 24 = 60.96 |
| 60 | 84.0 | 81.36 | 2.54 x 29 = 73.66 |
| 64 | 89.1 | 86.44 | 2.54 x 31 = 78.74 |


Marking No. 1 contact



No. 2 contact



No. 1 contact



Board drillings

For Performance Level 3 please specify digit 7
For Performance Level 2 please specify digit 6
S4 = 0.76 μm (30 μinch) Au or PdNi equivalent



Not normally kept in stock

- 1) No polarization slot for 6, 10 or 14 way
- 2) No polarization slot for 6 way
- 3) Pitch tolerance: ± 0.1

SEK