




## HARTING PushPull RJ45 – bulkhead

### Advantages

- Small, space-saving PushPull Interfaces in IP65 / IP67
- Easy connection of PushPull RJ45 system cords
- Screwable with 2 x M3 screws

### Technical characteristics

|   |   |
|---|---|
| Locking   | PushPull Technology<br>acc. to IEC 61 076-3-106 variant 4           |
| Number of contacts  | 8   |
| Transmission category   | Cat. 6, performance class EA,<br>suitable for 1/10 Gigabit Ethernet |
| Transmission rate   | 10/100 Mbit/s / 1/10 Gbit/s   |
| Shielding   | fully shielded,<br>360° shielding contact                           |
| Mating cycles   | min. 750  |
| Degree of protection  | IP65 / IP67   |
| Temperature range   | -40 °C ... +70 °C   |
| Housing material  | Plastic, black  |
| Flammability<br>acc. to UL 94   | V0  |
|  | UL approval (E102079)   |

| Identification | Part number | Drawing | Dimensions in mm |
|----------------|-------------|---------|------------------|
|----------------|-------------|---------|------------------|

HARTING PushPull RJ45 –  
bulkhead

09 45 345 1560

