



Identification

Part No.

Drawing


Dimensions in mm

**HARTING PushPull
Outdoor cable, RJ45, 4-wire**


- Length: a = 1.5 m
 a = 3.0 m
 a = 5.0 m
 a = 10.0 m
 a = 20.0 m

- 09 47 363 6069
 09 47 363 6071
 09 47 363 6073
 09 47 363 6078
 09 47 363 6080

double ended



a = length




**Han® 3 A
Outdoor cable, RJ45, 4-wire**


- Length: a = 1.5 m
 a = 3.0 m
 a = 5.0 m
 a = 10.0 m
 a = 20.0 m

- 09 45 715 0064
 09 45 715 0066
 09 45 715 0068
 09 45 715 0073
 09 45 715 0075

double ended



a = length



**Outdoor cable 4-wire, RJ45,
Cat. 5, PVC**

- Length: 20 m ring
 Length: 50 m ring
 Length: 100 m ring
 Length: 500 m reel

- 09 45 600 0135
 09 45 600 0145
 09 45 600 0105
 09 45 600 0115



- Wire: stranded tinned copper, AWG 22/7
 Overall screen: aluminate foil overlapped, tinned copper wire braid, braid coverage about 85 %
 Overall diameter: 6.3 – 6.7 mm