



Identification

Part No.

Drawing


Dimensions in mm

**HARTING PushPull
Outdoor cable, RJ45,
8-wire, Cat. 6**


- Length: a = 1.5 m
 a = 3.0 m
 a = 5.0 m
 a = 10.0 m
 a = 20.0 m

- 09 45 745 1578
 09 45 745 1580
 09 45 745 1582
 09 45 745 1587
 09 45 745 1589

double ended



a = length




**Han® 3 A
Outdoor cable, RJ45,
8-wire, Cat. 6**


- Length: a = 1.5 m
 a = 3.0 m
 a = 5.0 m
 a = 10.0 m
 a = 20.0 m

- 09 45 715 1583
 09 45 715 1585
 09 45 715 1587
 09 45 715 1592
 09 45 715 1594

double ended



a = length



**Outdoor cable 8-wire, RJ45,
Cat. 6, PVC**

- Length: 20 m ring
 Length: 50 m ring
 Length: 100 m ring
 Length: 500 m reel

- 09 45 600 0531
 09 45 600 0541
 09 45 600 0501
 09 45 600 0521



- Wire: bare stranded copper, AWG 27/7
 Pairs: aluminate foil overlapped PIMF
 Overall screen: tinned copper wire braid, braid coverage about 60 %
 Overall diameter: 6.3 – 6.9 mm