



Han® 3 A RJ45
 System cable, 8-wire
 RJ45 connector cable Han® 3 A for IP65 / IP67 applications

PVC / PUR	<input checked="" type="checkbox"/>	8 wire	<input checked="" type="checkbox"/>	4 wire	<input type="checkbox"/>	Cat. 5e	<input type="checkbox"/>	Cat. 6	<input checked="" type="checkbox"/>	Cat. 6A	<input type="checkbox"/>	Cat. 7	<input type="checkbox"/>
-----------	-------------------------------------	--------	-------------------------------------	--------	--------------------------	---------	--------------------------	--------	-------------------------------------	---------	--------------------------	--------	--------------------------

Connector types	Han® 3 A RJ45
Cable types	4 x 2, Twisted Pair, shielded
Sheath material	PVC / PUR
Wiring	8-pole, 1:1
Transmission performance	Category 6 / Class E up to 250 MHz acc. to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100/1000 Mbit/s
Shielding	Fully shielded, 360° shielding contact
Operating temperature range	-10 °C ... +70 °C
Standard lengths	1.5 m / 3 m / 5 m / 10 m / 20 m other lengths available on request
Colour	Yellow

- Advantages**
- Very robust metal housing Han® 3 A for IP65 / IP67
 - Additional locking

Identification	Part number		Drawing	Dimensions in mm
	PVC	PUR		
Han® 3 A RJ45 System cable, 8-wire	Yellow	Yellow		
Length 1.5 m	09 45 715 1523	09 45 715 1563		
Length 3.0 m	09 45 715 1525	09 45 715 1565		
Length 5.0 m	09 45 715 1527	09 45 715 1567		
Length 10.0 m	09 45 715 1551	09 45 715 1572		
Length 20.0 m	09 45 715 1553	09 45 715 1574		