

Pin shroud



Number of contacts

48

Pin shrouds
for type F "low profile"
with press-in pins 13 mm



Identification	pcb-thickness ± 10 %	Dimension X ± 0.1	Part number
Pin shrouds suitable for shell housing D20			
without locking levers with press-in nuts	1.6 - 2.4	1.6	09 06 002 9922
without locking levers with press-in nuts	3.2 - 4.0	0	09 06 002 9921

DIN Power
up to 6 A

Dimensions

Einpressmutter M2,5
press-in nut M2,5

15 x 5,08 = (76,2)

5,08 1,27 3,81

16,6

105,5

B

B

Einpressmutter M2,5
press-in nut M2,5

A-A (2:1) 90°

14,7±0,1

12,75±0,05

8,3±0,1

3±0,1

3,81

2x 3,81 = (7,62)

B-B (2:1) 90°

5,8±0,15

97,5±0,1

90±0,1

85,5±0,1

0,3±0,1

8,6±0,05

Reihe
row

z

b

d

2

A

32

Position
position

x

Dimensions in mm