


Number of contacts

max. 24



Female connectors

Identification	No. of contacts	Part number	Drawing	Dimensions in mm
<p>Female connector for crimp contacts</p> <p>Order contacts separately see page 03.33</p>	24	09 26 024 3201 ^{f)}		
<p>Shell housing A with integrated fixing screws</p> <p>Supplied with: Shell 2x Locking screw 2x Screw M3x10 2x Nut M3 2x Screw BZ 2.9x9.5 2x Cable clamp 1x Tension relief 1x</p>		09 26 024 0401 ^{f)}		
<p>Open hood</p> <p>Supplied with: Open hood 1x Locking screw 2x Screw BZ 2.2x9.5 2x Cable tie 1x</p>		09 26 000 9901 ^{f)}		

DIN Power up to 6 A

^{f)} Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2