


Number of contacts

30, 20



Female connectors

DIN Signal up to 2 A

Identification	No. of contacts	Contact arrangement	Part number	Performance levels according to IEC 60 603-2.	
				3	2 1
Female connector with solder pins 2.9 mm with fixing flange	30		Performance level 3 on request	09 25 230 6824	Performance level 1 on request
	20				
	30			09 25 230 6841 ^{d)}	
	30			09 25 230 6414 ^{d)}	
Female connector with solder pins 4.5 mm with fixing flange	30			09 25 230 6825	
	20			09 25 220 6825	
Female connector with solder pins 13 mm with fixing flange	30			09 25 230 6421	
Female connector with press-in pins 4.5 mm with fixing flange	30			09 25 230 6850	
	30		09 25 230 6870		

Identification	No. of contacts	Part number	Drawing	Dimensions in mm
Female connector for crimp contacts Order contacts separately see page 01.28				
Type 3C	30	09 25 030 3214 ^{f)}		
Type 3C Position marking turned for mating type 3R male	30	09 25 030 3217 ^{f)}		

^{d)} CTI > 400

^{f)} Railway classification NFF 16-101, Smoke index: F1, Flammability class: I2