



Unmanaged Plug-and-Play Ethernet Switches
 for Assembly on DIN Rail in Control Cabinets
 Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C
 Power Sourcing Equipment (PSE) with 4 PoE+ ports (34.2 watts per port)

Specification

Number of ports copper / termination	4 x 10BASE-Te / 100BASE-TX EEE / 1000BASE-T EEE RJ45 (twisted pair)
including PoE+ ports	4 x PoE+ with 34.2 watts per port
Number of ports F.O. / termination	3 x 100/1000 SFP
Nominal voltage	24 / 48 / 54 VDC ≡
Permissible voltage range	9 V ... 60 VDC ≡
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / ≡)
Current consumption typical @ 24 V	See eCatalogue
Dimensions (W x H x D)	25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	See eCatalogue
MTBF	See eCatalogue
Approvals	CE
Approvals (in preparation)	Federal Communications Commission (FCC), cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawings	Dimensions in mm
----------------	-------------	----------	------------------

Ha-VIS eCon
 3043GB-AC-P
 0 °C ... +55 °C
 3 x SFP

24 03 404 3330

Ha-VIS eCon
 3043GBT-AC-P
 -40 °C ... +70 °C
 3 x SFP

24 03 404 3320

