


Number of contacts

30, 20



Male connectors

Identification	Number of contacts	Contact arrangement	Part No.	Performance levels according to IEC 60603-2.	
			3	2	1
Male connector with solder pins 2.5 mm with fixing flange with fixing flange, SMC without fixing flange without fixing flange, SMC	30		Performance level 3 on request	09 29 130 6902	Performance level 1 on request
	20			09 29 120 6902	
	30			09 29 130 6519 ^{d)}	
	30			09 29 130 6592	
	30			09 29 130 6569 ^{d)}	
Male connector with solder pins 4.0 mm with fixing flange with fixing flange, SMC without fixing flange without fixing flange, SMC	30			09 29 130 6903	
	20			09 29 120 6903	
	30			09 29 130 6520 ^{d)}	
	30			09 29 130 6593	
	30			09 29 130 6570 ^{d)}	
Male connector with solder pins 13 mm with fixing flange with fixing flange, SMC	30			09 29 130 6577	
	20			09 29 120 6577	
	30			09 29 130 6521 ^{d)}	
Male connector with wrap posts ¹⁾ 13 mm with fixing flange	30			09 29 130 6907	
Male connector with press-in pins 5.0 mm with fixing flange without fixing flange	30			09 29 130 6904	
	20		09 29 120 6904		
	30		09 29 130 6504		
Male connector with press-in pins 13 mm with fixing flange without fixing flange	30		09 29 130 6985 09 29 130 6974*		
	20		09 29 120 6974*		
	30		09 29 130 6574*		

* Wrap posts for interfacing selectively gold plated (performance level 3)
¹⁾ To be used only for wire wrap termination
^{d)} CTI > 400