


















Identification	Part number	Size	Drawing	Dimensions in mm
Han® Ex Q7 Set Order crimp contacts separately 	10 36 007 0001	3 A	M  F  Panel cut out: 22 x 22 mm	  Contact arrangement view: termination side
Han® Ex 8D Set Order crimp contacts separately 	10 36 008 0006	3 A	M  F  Panel cut out: 22 x 22 mm	 
Han® Ex Q12 Set Order crimp contacts separately 	10 36 012 0001	3 A	M  F  Panel cut out: 22 x 22 mm	 

Identification	Wire gauge mm ²	Partnumber		Drawing	Dimensions in mm																					
		Male contact	Female contact																							
Crimp contact silver plated 	0.14-0.37 0.5 0.75 1.0 1.5 2.5	09 15 000 6104 09 15 000 6103 09 15 000 6105 09 15 000 6102 09 15 000 6101 09 15 000 6106	09 15 000 6204 09 15 000 6203 09 15 000 6205 09 15 000 6202 09 15 000 6201 09 15 000 6206		<table border="1"> <thead> <tr> <th>Wire gauge</th> <th>Ø mm</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.14-0.37 mm²</td> <td>AWG 26-22</td> <td>0.9</td> </tr> <tr> <td>0.5 mm²</td> <td>AWG 20</td> <td>1.1</td> </tr> <tr> <td>0.75 mm²</td> <td>AWG 18</td> <td>1.3</td> </tr> <tr> <td>1.0 mm²</td> <td>AWG 18</td> <td>1.45</td> </tr> <tr> <td>1.5 mm²</td> <td>AWG 16</td> <td>1.75</td> </tr> <tr> <td>2.5 mm²</td> <td>AWG 14</td> <td>2.25</td> </tr> </tbody> </table>	Wire gauge	Ø mm	Stripping length	0.14-0.37 mm ²	AWG 26-22	0.9	0.5 mm ²	AWG 20	1.1	0.75 mm ²	AWG 18	1.3	1.0 mm ²	AWG 18	1.45	1.5 mm ²	AWG 16	1.75	2.5 mm ²	AWG 14	2.25
Wire gauge	Ø mm	Stripping length																								
0.14-0.37 mm ²	AWG 26-22	0.9																								
0.5 mm ²	AWG 20	1.1																								
0.75 mm ²	AWG 18	1.3																								
1.0 mm ²	AWG 18	1.45																								
1.5 mm ²	AWG 16	1.75																								
2.5 mm ²	AWG 14	2.25																								