














1 contact + shielding with crimp flange

Identification	Part number		Drawing	Dimensions in mm
	Male insert (M)	Female insert (F)		
<p><b>Han® ETCS inserts</b></p> <p>Order Han® Coax ETCS contacts separately</p> 	09 15 001 3004	09 15 001 3104	<p>M</p>  <p>F</p> 	 

Identification	Wire gauge mm <sup>2</sup>	Part number		Drawing	Dimensions in mm
		Male contact	Female contact		
<p><b>Han® Coax ETCS contacts</b></p> <p>1 + shielding, 50 Ω for Han E® crimp contacts</p> 	—	09 15 001 6101	09 15 001 6201	<p>M</p>  <p>F</p> 	 
<p><b>Han E® contacts</b></p> <p>gold plated</p> 	0.14-0.37 0.5 0.75 1.0 1.5 2.5 4.0 5.5	09 33 000 6117 09 33 000 6122 09 33 000 6115 09 33 000 6118 09 33 000 6116 09 33 000 6123 09 33 000 6119 09 33 000 6139	09 33 000 6217 09 33 000 6222 09 33 000 6215 09 33 000 6218 09 33 000 6216 09 33 000 6223 09 33 000 6219 09 33 000 6239		