



Unmanaged Plug-and-Play Ethernet Switches
 for Assembly on DIN Rail in Control Cabinets
 Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

Specification

Number of ports copper / termination	8 x 10BASE-Te / 100BASE-TX EEE / RJ45 (twisted pair)
Nominal voltage	24 / 48 VDC ≐
Permissible voltage range	9 V ... 60 VDC ≐
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / ≐)
Current consumption typical @ 24 V	See eCatalogue
Dimensions (W x H x D)	25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	445 g
MTBF	See eCatalogue
Approvals	CE
Approvals (in preparation)	Federal Communications Commission (FCC), cUL US 508 listed Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawings	Dimensions in mm
----------------	-------------	----------	------------------

Ha-VIS eCon 3080B-A 0 °C ... +55 °C	24 03 008 0010
Ha-VIS eCon 3080BT-A -40 °C ... +70 °C	24 03 008 0000

