



Unmanaged Plug-and-Play Ethernet Switches  
for Assembly on DIN Rail in Control Cabinets

Commercial Temp.: 0 °C ... +55 °C / Industrial Temp.: -40 °C ... +70 °C

## Specification

Number of ports copper / termination	4 x 10BASE-Te / 100BASE-TX EEE / RJ45 (twisted pair)
Number of ports F.O. / termination	2 x 100BASE-FX / SC duplex socket
Nominal voltage	24 / 48 VDC =
Permissible voltage range	9 V ... 60 VDC =
Termination	Screw type terminal block, pluggable, 3-poles (+ / - / =)
Current consumption typical @ 24 V	See eCatalogue
Dimensions (W x H x D)	25.0 x 142.0 x 107.5 mm (without pluggable screw type terminal block)
Weight	445 g
MTBF	See eCatalogue
Approvals	CE
Approvals (in preparation)	Federal Communications Commission (FCC), cUL US 508 listed, Det Norske Veritas (DNV), Germanischer Lloyd (GL), American Bureau of Shipping (ABS), Nippon Kaiji Kyokai (NK)

Identification	Part number	Drawings	Dimensions in mm
----------------	-------------	----------	------------------

Ha-VIS eCon 3042B-AD 0 °C ... +55 °C 2 x MM (2 km)	24 03 004 2110	
Ha-VIS eCon 3042B-AF 0 °C ... +55 °C 2 x SM (15 km)	24 03 004 2210	
Ha-VIS eCon 3042BT-AD -40 °C ... +70 °C 2 x MM (2 km)	24 03 004 2100	
Ha-VIS eCon 3042BT-AF -40 °C ... +70 °C 2 x SM (15 km)	24 03 004 2200	