




Number of contacts

25

4 A 50 V 0.8 kV 3

Identification	Conductor cross-section (mm ²)	Part number		Drawing (dimensions in mm)												
		Male	Female													
<p>Han-Modular®, Han® High Density module, Crimp termination</p>  <p>Please order crimp contacts separately.</p>	0.09 ... 0.52	09 14 025 3001	09 14 025 3101	 <p>Contact arrangement (view from termination side)</p>												
<p>D-Sub, Crimp contact, Contact surface: HMC gold plated</p> 	0.08 ... 0.21 0.13 ... 0.33 0.33 ... 0.52	09 67 000 7570 09 67 000 5570 09 67 000 8570	09 67 000 7470 09 67 000 5470 09 67 000 8470	<table border="1"> <thead> <tr> <th>Conductor cross-section</th> <th>∅</th> <th>Stripping length</th> </tr> </thead> <tbody> <tr> <td>0.08 - 0.21 mm²</td> <td>AWG 28-24</td> <td>4 mm</td> </tr> <tr> <td>0.13 - 0.33 mm²</td> <td>AWG 26-22</td> <td>4 mm</td> </tr> <tr> <td>0.33 - 0.52 mm²</td> <td>AWG 22-20</td> <td>4 mm</td> </tr> </tbody> </table>	Conductor cross-section	∅	Stripping length	0.08 - 0.21 mm ²	AWG 28-24	4 mm	0.13 - 0.33 mm ²	AWG 26-22	4 mm	0.33 - 0.52 mm ²	AWG 22-20	4 mm
Conductor cross-section	∅	Stripping length														
0.08 - 0.21 mm ²	AWG 28-24	4 mm														
0.13 - 0.33 mm ²	AWG 26-22	4 mm														
0.33 - 0.52 mm ²	AWG 22-20	4 mm														

Han
HMC