

Hoods/housings for harsh environments
Single locking lever

High
Temp

Technical characteristics

Limiting temperature	-40 ... +125 °C, -40 ... +200 °C With Han® High Temp components
Degree of protection acc. to IEC 60529	IP65, IP67
Type rating acc. to UL 50 / UL 50E	4, 4X, 12
Material (hood/housing)	Stainless steel
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
Material (locking)	Stainless steel

Technical characteristics

RoHS compliant

Specifications and approvals

UL 1977 ECBT2.E235076
CSA-C22.2 No. 182.3 ECBT8.E235076
DNV GL



Identification	Cable entry	Part number	Drawing (dimensions in mm)
Han-INOX®, Han® High Temp, Hood, Top entry, IP65, IP67 Pack contents: With seal screw	1x M20	19 44 003 1440	
Han-INOX®, Han® High Temp, Bulkhead mounted housing, Straight, IP65, IP67 Pack contents: With seal screw		19 44 003 0301	