










## Technical characteristics

Material (accessories) NBR

## Technical characteristics

Colour (accessories) Black  
RoHS compliant

Identification	Clamping range (mm)	Part number	Drawing (dimensions in mm)
Cable entry seal, 4 cable entries, Wide version  	... 6	09 00 000 6004	
Cable entry seal, 1 cable entry, Narrow version  	4.5 ... 6 6 ... 7.5 7.5 ... 9	09 00 000 6005 09 00 000 6006 09 00 000 6007	
Cable entry seal, 1 cable entry, Wide version  	9 ... 10.5 10.5 ... 12 12 ... 13.5 13.5 ... 15 15 ... 16	09 00 000 6008 09 00 000 6009 09 00 000 6010 09 00 000 6011 09 00 000 6012	
Dummy plugs, Narrow version  		09 00 000 6101	
Dummy plugs, Wide version  		09 00 000 6102	