

PCB distance	<i>har-modular</i> <sup>®</sup>			
16.8 - 18.6 mm	Fixing rails	The modules are combined to each other by two fixing rails. Please choose depending on total length of your connector.	Connector length	Part number
		<i>har-modular</i> <sup>®</sup> fixing rail 20.22	20.32 mm	02 09 500 1004
		<i>har-modular</i> <sup>®</sup> fixing rail 25.30	25.40 mm	02 09 500 1005
		<i>har-modular</i> <sup>®</sup> fixing rail 30.38	30.48 mm	02 09 500 1006
		<i>har-modular</i> <sup>®</sup> fixing rail 35.46	35.56 mm	02 09 500 1007
		<i>har-modular</i> <sup>®</sup> fixing rail 40.54	40.64 mm	02 09 500 1008
		<i>har-modular</i> <sup>®</sup> fixing rail 45.62	45.72 mm	02 09 500 1009
		<i>har-modular</i> <sup>®</sup> fixing rail 50.70	50.80 mm	02 09 500 1010
		<i>har-modular</i> <sup>®</sup> fixing rail 55.78	55.88 mm	02 09 500 1011
		<i>har-modular</i> <sup>®</sup> fixing rail 60.86	60.96 mm	02 09 500 1012
		<i>har-modular</i> <sup>®</sup> fixing rail 65.94	66.04 mm	02 09 500 1013
		<i>har-modular</i> <sup>®</sup> fixing rail 71.02	71.12 mm	02 09 500 1014
		<i>har-modular</i> <sup>®</sup> fixing rail 76.10	76.20 mm	02 09 500 1015
		<i>har-modular</i> <sup>®</sup> fixing rail 81.18	81.28 mm	02 09 500 1016
		<i>har-modular</i> <sup>®</sup> fixing rail 86.26	86.36 mm	02 09 500 1017
		<i>har-modular</i> <sup>®</sup> fixing rail 91.34	91.44 mm	02 09 500 1018
		<i>har-modular</i> <sup>®</sup> fixing rail 96.42	96.52 mm	02 09 500 1019
		<i>har-modular</i> <sup>®</sup> fixing rail 101.50	101.60 mm	02 09 500 1020
		<i>har-modular</i> <sup>®</sup> fixing rail 106.58	106.68 mm	02 09 500 1021
		<i>har-modular</i> <sup>®</sup> fixing rail 111.66	111.76 mm	02 09 500 1022
		<i>har-modular</i> <sup>®</sup> fixing rail 116.74	116.84 mm	02 09 500 1023
		<i>har-modular</i> <sup>®</sup> fixing rail 121.82	121.92 mm	02 09 500 1024
		<i>har-modular</i> <sup>®</sup> fixing rail 126.90	127.00 mm	02 09 500 1025
		<i>har-modular</i> <sup>®</sup> fixing rail 131.98	132.08 mm	02 09 500 1026
		<i>har-modular</i> <sup>®</sup> fixing rail 137.06	137.16 mm	02 09 500 1027
		<i>har-modular</i> <sup>®</sup> fixing rail 142.14	142.24 mm	02 09 500 1028
		<i>har-modular</i> <sup>®</sup> fixing rail 147.22	147.32 mm	02 09 500 1029
		<i>har-modular</i> <sup>®</sup> fixing rail 152.30	152.40 mm	02 09 500 1030
<i>har-modular</i> <sup>®</sup> fixing rail 157.38	157.48 mm	02 09 500 1031		
<i>har-modular</i> <sup>®</sup> fixing rail 162.46	162.56 mm	02 09 500 1032		
<i>har-modular</i> <sup>®</sup> fixing rail 167.54	167.64 mm	02 09 500 1033		
<i>har-modular</i> <sup>®</sup> fixing rail 172.62	172.72 mm	02 09 500 1034		