



HARTING PushPull USB System cables

Advantages

- Compatible with HARTING PushPull bulkhead mounting housings 09 45 545 0028 and 09 45 545 0032
- Plug+Play solutions for e.g. device integration and switch cabinets
- USB 2.0 and 3.0 compatible
- Fully shielded, 360° shielding contact
- Robust design, suitable for industrial applications

Technical characteristics

Mating face	USB 2.0 / 3.0 type A
Number of contacts	USB 2.0: 4 and USB 3.0: 9
Degree of protection	IP65 / IP67 for PushPull interfaces IP20 for USB interfaces
Mating cycles	min. 750
Temperature range	-40 °C ... +70 °C

Identification	Part number	Drawing	Dimensions in mm
System cables			
USB 2.0 type A jack to connector	Length a:	0.5 m	09 45 545 1920
		1.0 m	09 45 545 1921
		1.5 m	09 45 545 1922
		2.0 m	09 45 545 1923
		3.0 m	09 45 545 1924
		5.0 m	09 45 545 1925
USB 3.0 type A jack to connector	Length a:	0.5 m	09 45 545 1930
		1.0 m	09 45 545 1931
		1.5 m	09 45 545 1932
		2.0 m	09 45 545 1933
		3.0 m	09 45 545 1934

Other types and lengths on request