


PushPull RJ45 IP65/IP67 connectors



HARTING PushPull,
type acc. to IEC 61076-3-106 variant 4
Housing bulkhead mounting and housing cable-to-cable combinations

Identification	Part number	Drawing	Dimensions in mm
RJ45 female inserts ② Cat. 5, 4 poles, 10/100 Mbit/s IDC for AWG 24-22 solid and stranded Cat. 6 _A , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 28-24 solid and stranded Cat. 6 _A , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 24-22 solid and stranded Cat. 6 _A , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 23/22 solid and stranded Cat. 6 _A , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 27/26 solid and stranded Cat. 6 _A , 8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001 / 20 82 000 0003) Cat. 6, 8 poles, 10/100 Mbit/s and 1/10 Gbit/s RJ45 system cable jack on connector 0.15 m 10.0 m	09 45 545 1120 09 45 545 1561 09 45 545 1562 20 82 001 0001 20 82 001 0002 20 82 000 0002 09 45 545 1500 up to 09 45 545 1518	 	13,15 15,6
HARTING PushPull Housing cable-to-cable ③ plastic, black for cable outer diameter 6.5 ... 9.5 mm HARTING PushPull Housing bulkhead mounting extern, plastic, black (Not combinable with EasyInstall Housing bulkhead mounting 09 45 545 0032!)	09 45 345 0000 09 45 345 0001	2X M2.5x10 self tapping screws according to EN ISO 7092 2X M2.5x10 self tapping screws according to EN ISO 7092 	65,5 50 21 1,5 59,2 21 1,5