



HARTING PushPull acc. to IEC 61 076-3-106 variant 4
RJ45 Outlet, Cat. 6, 8 poles

Advantages

- Simple mounting
- Cable entering optionally from bottom or from top side
- Self-closing protection caps in IP65/IP67
- IP65/IP67 label

Technical characteristics

Number of ports, Copper / Termination	2 x HARTING PushPull (V4) RJ45 (IP65/IP67)
Transmission performance	Category 6 / Class E up to 250 MHz according to ISO/IEC 11 801:2002, EN 50 173-1
Transmission rate	10/100/1000 Mbit/s
Termination	Via IDC contacts, tool-less
Wire gauge	AWG 24 ... 22 (0.25 mm ² ... 0.34 mm ²) solid and stranded
Strand diameter	0.7 mm ... 1.6 mm
Cable diameter	6 mm ... 9 mm
Shielding	Fully shielded, 360° shielding contact
Mounting	Wall mounting
Dimensions (H x W x D)	152 x 90 x 69 mm
Degree of protection	IP65/IP67
Operating temperature range	-20 °C ... +70 °C
Housing material	polycarbonate, UL94 V-0
Colour	Black (similar RAL 9011) or White (similar RAL 9010)

Connecting hardware

Identification	Part number	Drawing	Dimensions in mm
----------------	-------------	---------	------------------

HARTING PushPull RJ45 Outlet

Black
white

09 45 845 1500
09 45 845 1501

consisting of:
2-port outlet housing with protection caps, cable management, cable glands and label
2x RJ45 female modules, Category 6
1x blind plug (if only only 1 cable is used)
Assembly instructions

