



Han® 3 A RJ45 10G Cat. 6 – panel feed-throughs

## Advantages

- Compact and robust design
- 360° shielding
- Easy mounting
- Transmission Category 6, performance class E<sub>A</sub>, suitable for 1/10 Gigabit Ethernet
- RJ45 mating compatible
- Coding (4 variants) possible

## Technical characteristics

Number of ports	2 / 1x Han® 3 A RJ45 (IP65/IP67) 1x RJ45 (IP20)
Transmission performance	Category 6 / Class E <sub>A</sub> acc. to ISO/IEC 11801:2002, EN 50 173-1
Transmission rate	10/100 Mbit/s and 1/10 Gbit/s
Shielding	Fully shielded, 360° shielding contact
Mounting	Screwable to cover plates
Degree of protection	IP65/IP67
Mating cycles	min. 500
Temperature range	-40 °C ... + 70 °C
Housing material	
Plastic version	polycarbonate, black, UL 94 V0
Metal version	Zinc die-cast, powder-coated

Identification	Part number	Drawing	Dimensions in mm
<b>Panel feed-through set, 8 poles</b> Plastic version, black Metal version Standard, grey Metal version M, black  Metal version Standard, grey, with self-closing protective cap	09 45 225 1560 09 45 215 1560 09 45 215 1561  09 45 215 1562		
<b>Han® 3 A RJ45 10G insert Cat. 6</b> (for Han® 3 A housings)	09 45 200 1560		