



## Han® 3 A RJ45 Hybrid IP65/IP67 connectors

Identification	Part number	Drawing	Dimensions in mm
<b>Han® 3 A RJ45 female inserts</b> <span style="float: right;">①</span>  Cat. 5, 4 poles, 10/100 Mbit/s IDC for AWG 24-22 solid and stranded  Cat. 6, 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 28-24 solid and stranded  Cat. 6, 8 poles, 10/100 Mbit/s and 1/10 Gbit/s IDC for AWG 24-22 solid and stranded  Cat. 6 <sub>A</sub> , 4/8 poles, 10/100 Mbit/s and 1/10 Gbit/s preLink® IDC for AWG 23/22 or AWG 27/26 depending on the separately orderable preLink® terminal module (20 82 000 0001/20 82 000 0003)  Cat. 6, 8 poles, 10/100 Mbit/s and 1/10 Gbit/s RJ45 system cable jack on connector  0.15 m ... 10.0 m	09 45 545 1120  09 45 545 1561  09 45 545 1562  20 82 001 0001  09 45 545 1500 ... 09 45 545 1518	  	
<b>Han® 3 A RJ45 Hybrid adapter for HIFF inserts with power modules</b> <span style="float: right;">②</span>	09 45 200 1760		
<b>Han® housing</b> <span style="float: right;">③</span>  Housing bulkhead mounting: – metal, grey – metal, black – metal, EMC	10 12 005 1004 09 45 515 0027 09 45 515 0028		