



Identification	Part number
<p><b>HARTING RJ Industrial®</b> system cable, angled, 4-wire Type A, angeld top to angled bottom</p> <p style="text-align: right;">Length 0.5 m 1.0 m 1.5 m 2.0 m 3.0 m 5.0 m</p>	<p>09 47 030 4001 09 47 030 4002 09 47 030 4003 09 47 030 4004 09 47 030 4005 09 47 030 4007</p>
<p><b>HARTING RJ Industrial®</b> system cable, angled, 4-wire Type B, angeld top to angled bottom</p> <p style="text-align: right;">Length 0.5 m 1.0 m 1.5 m 2.0 m 3.0 m 5.0 m</p>	<p>09 47 030 4023 09 47 030 4024 09 47 030 4025 09 47 030 4026 09 47 030 4027 09 47 030 4029</p>
<p><b>HARTING RJ Industrial®</b> system cable, angled, 4-wire Type C, angeld top to angled bottom</p> <p style="text-align: right;">Length 0.5 m 1.0 m 1.5 m 2.0 m 3.0 m 5.0 m</p>	<p>09 47 030 4045 09 47 030 4046 09 47 030 4047 09 47 030 4048 09 47 030 4049 09 47 030 4051</p>
<p><b>HARTING RJ Industrial®</b> system cable, angled, 4-wire Outdoor, angeld top to angled bottom</p> <p style="text-align: right;">Length 0.5 m 1.0 m 1.5 m 2.0 m 3.0 m 5.0 m</p>	<p>09 47 030 4067 09 47 030 4068 09 47 030 4069 09 47 030 4070 09 47 030 4071 09 47 030 4073</p>

Other cable lengths on request